

SENSOR OPERATED

Dualflow Plus with brushless motor



M24A
White finish



M24AB
Matte black finish



M24ABT
Matte total black finish



M24ACS
Satin finish

General description


- Automatic double-sided high-speed hand dryer with maintenance-free brushless motor, ensuring long lifespan, ideal for an intensive usage and, therefore, suitable for high traffic facilities.
- Water collection area with no-splash design, which prevents the residual water from drying hands to end up on the floor, thus keeping it dry and preventing slipping hazard.
- Dualflow Plus is a touchless hand dryer because it starts and stops automatically thanks to a pair of IR sensors in both sides of the device for automatic hands detection, creating, therefore, the optimal hygienic conditions because it confines the growth of bacteria.
- It incorporates an HEPA media filter that filters the solid particles in suspension (pollen, dust mites, tobacco smoke, etc.) significantly improving air quality.
- Proven antimicrobial and antibacterial protection using silver ion technology from Biocote®, providing a total antimicrobial solution. These ions inhibit the reproduction of micro-organisms in the product throughout its lifetime.
- It can be delivered, optionally, with an ionizer ("Ion Hygienic" technology) that purifies the air through negatively charged particles (anions), eliminating most of the particles and germs carried by the air, making it healthier and purer.
- Universal voltage. It works indistinctly at electrical voltages of 100-120 V or 220-240 V.
- Motor power adjustable, allowing electricity consumption to be regulated (between 250 and 1,100W).
- Maximum air speed 410 Km/h.
- Dries hands in only 8 / 15 seconds.
- 30 second maximum continuous running time.
- Lowest noise level in its category. (62 dBA in ECO mode).
- Optionally, and by means of a kit for the connection to the waste pipe, code KITDESM14A, the Dualflow Plus can be connected directly to the waste pipe.
- 5-Year Warranty.

Components and materials

- COVER:** made of high impact ABS, 3 mm thick.
- BASE PLATE:** made of plastic PA6V0.
- MOTOR:** extremely durable high-speed Class F brushless motor, maintenance free, with adjustable power, allowing electricity consumption and sound pressure to be regulated.
- HEATING ELEMENT:** minimum waved wire NiCr heating element of 200W, mounted on a mica frame that incorporates a self-resetable thermal cut-off which disconnect the whole appliance. The heating element can be disconnected by means of an ON/OFF switch.

Technical Specifications

| | |
|--|---|
| Voltage | 100 - 240V |
| Frequency | 50/60Hz |
| Electrical Isolation | Class I |
| Total power | 250 – 1,100W |
| Consumption | 1.3 – 4.8A |
| Motor power | 900W |
| Rpm | 17,600 – 27,600 |
| Heating element power | 200W or 0W (ON/OFF switch) |
| Dimensions | 665x320x228 mm |
| Weight | 8.5Kg |
| Cover thickness | 3mm |
| Drying time | 8-15sec |
| Effective airflow | 101 - 177 m ³ /h (1,680 - 2,950 l/min) |
| Air velocity | 234 – 410Km/h |
| Air temperature (10 cm distance/23°C) | 38°C |
| Sound pressure (at 2m) | 62 – 72dBA |
| Protection rating | IPX4 |



Dimensions: ±4%

- **HEPA MEDIA FILTER:** cartridge that holds an HEPA media filter that filters suspended solid particles (pollen, dust mites, cigarette smoke, etc.), notably improving the air quality. Furthermore, this cartridge also contains an activated carbon filtering media that neutralizes odours and absorbs fumes and gases, helping avoid bad odours.
- **IONIZER:** cleans and purifies the air through negative ions (anions) which remove microscopic particles from the air making it healthier (optional).
- **CONNECTION TO THE WASTE PIPE:** optionally, and by means of a kit for the connection to the waste pipe, code KITDESM24A, the Dualflow Plus can be connected directly to the waste pipe. Thus, the emptying of the water tank is eliminated because the water always goes directly to the waste pipe.
- **INNER TANK:** collects the water. It is removable and it has an external valve for easy emptying.
- Optionally, and by means of a kit for the connection to the waste pipe, code KITDESM24A, the Dualflow Plus can be connected directly to the waste pipe.
- **AUTO CHECK-IN LIGHTING PANEL:** for fast diagnosis of the dryer (green - machine running, blue - full tank, red - check engine).
Optical and acoustic warning of full tank.
- **ODOR NEUTRALIZER:** for a cleaner and more pleasant atmosphere in the bathroom. (optional).

Codes

| Cover material | Cover finish | HAND DRYER CODES | | | |
|----------------|-------------------|--|-----------------------------------|--------------|---|
| | | Neither connection to the waste pipe nor ionizer | With connection to the waste pipe | With ionizer | With connection to the waste pipe and ionizer |
| ABS | White | M24A | M24A-DES | M24A-I | M24A-DES-I |
| ABS | Matte black | M24AB | M24AB-DES | M24AB-I | M24AB-DES-I |
| ABS | Matte total black | M24ABT | M24ABT-DES | M24ABT-I | M24ABT-DES-I |
| ABS | Satin | M24ACS | M24ACS-DES | M24ACS-I | M24ACS-DES-I |

Operation

Place the hands between the air outflow valves, inside the hand dryer. The dryer will start automatically, and go on with no interruption as long as the hands are kept in the detection range of the sensor. Move the hands vertically in order to dry them completely. The appliance will stop 2 seconds after the hands are removed from the airflow.







Text for prescription

Hands-in automatic hand dryer shall be equipped with infrared sensors on both upper sides (barrier-type detection). The unit shall weigh 8,50 kg. The housing shall be made of ABS and shall be available in 4 finishes: white, matte black, matte total black and satin. The housing shall have a thickness of 3 mm. The dryer shall be equipped with a brushless Class F motor, with an adjustable speed range from 17.600 to 27.600 rpm and motor power between 250 and 900 W. It shall include a heating element with on/off switch and a power of 200 W. The unit shall operate at a frequency of 50/60 Hz and voltage of 100-240 V, with a total power range of 250 to 1.100 W with a consumption of 1,3 to 4,8 A. Drying time shall be 8 to 10 seconds with an airspeed of 234–410 km/h. The unit shall incorporate a HEPA filter as standard, an optional ionizer, and antimicrobial protection based on silver- ion technology on all user-contact surfaces. The dryer shall be equipped with a removable water collection tank with a volume of 0,5 L and an option for drainage connection. The unit shall be HACCP certified. The unit shall comply with the applicable standards for hand dryers (EN 60335-1, EN 60335-2-23, EN 61000-3-2, and EN 61000-3-3).

Mounting


Recommended heights distance from the floor



| | | | |
|-----|---|---|---|
| |  |  |  |
| Z = | 92 cm (36 1/4") | | 87 cm (34 1/4") |
| H = | 85 cm (33 1/2") | | 80 cm (31 1/2") |
| y = | 57 cm (22 1/2") | | 52 cm (20 1/2") |


Connection to the waste pipe

1




Break the flap on the rear side of the hand dryer base.
Use a screwdriver and a hammer to do it more easily

2




Disassemble the frontal cover and cut the original drain tube skim to the plastic union using a cutter

3




Introduce one end of the new tube through the new hole in the backside and fix the other side over the remaining part of the cut old tube using the provided flange

4




Confirm that the new tube maintains a "U" shape once assembled and connect the backside part of the tube to the waste pipe. Finally, assemble the frontal cover.



If the hand dryer is installed according to the installation instructions (upper back part of the dryer at 920 mm height), the main drain pipe installation should be approximately 450 mm from the water outlet height to the floor.

For other installation heights, the proportions shown in the figure on the left side must be taken into account.

For more information about the connection to the waste pipe, watch the following video:



Certificates and Qualifications



Electromagnetic
Compatibility
Regular Production
Surveillance



Mediclinics, S.A., reserves the right to make changes and/or modifications to the products and their specifications without prior notice.
Review: 09-25 © mediclinics S.A.



8-OP-DO-FT